

BESSY VSR 1.5 GHz CAVITY DESIGN AND CONSIDERATIONS ON WAVEGUIDE DAMPING

A. Vélez, J. Knobloch and A. Neumann
Helmholtz Zentrum Berlin, Germany.

HZB Helmholtz
Zentrum Berlin

Abstract: The BESSY VSR upgrade of the BESSY II light source represents a novel approach to simultaneously store long (ca. 15ps) and short (ca. 1.5ps) bunches in the storage ring with the “standard” user optics. To this end, new high-voltage L-Band superconducting multi-cell cavities must be installed in one of the straights of the ring. These 1.5 GHz and 1.75 GHz cavities are based on 1.3 GHz systems being developed for the bERLinPro energy-recovery linac. This paper describes the baseline electromagnetic design of the first 5-cell cavity operating at 1.5 GHz as well different design approaches to ensure reliable operation.


Mid-Cell/Multi-Cell RF design

- **High CW Eacc** required (20MV/m)
- Starting point: JLAB/CORNELL models
- Mid-cell parametric optimization (challenging RF Specifications)

Table 1: RF current parameters

Param.	Units	Goal	Mid-Cell	5 Cell
Epk/Eacc	-	≤ 2.3	2.29	2.29
Bpk/Epk	mT/(MV/M)	≤ 2.3	1.816	1.91
R/Q	(Ω)	≥ 95	100.7	105*5
G	(Ω)		280.05	279

COMSOL → parametric calculations for Mid-cell geometry
HFSS → 3D calculations for Qext spectrum (PMLs)




HOMs damping is critical

- High Iris diameter $\phi=71.34\text{mm}$
- High cell to cell coupling for
- TM₀₁₀: **$K_c=3.3\%$**

Simetrical end cells

HFSS parametric studies
for field flatness
Including end groups
(**$ff=98.2\%$**)




SUMMARY

- Efficient dipole damping by using enlarged beam pipe is obtained (cut off below first dipole band)
- Damping improvement on dangerous modes (Monopole TM₀₁₁)
- Tuning waveguide technique shows significant improvement on damping the 2.8 GHz TE₀₁₁/TM₂₁₁ bands
- High cell to cell coupling is applied **$K_c=3.3\%$**



Damping Studies

- **HZB 5 cells** (beam pipe $\phi=71.34\text{mm}$)
- **HZB 5 cells enlarged beam pipe** ($\phi=105\text{mm}$)



Standard WG



Tuned WG



HZB 5 CELLS



HZB 5 CELLS ENLARGED BP.

